


# Powering Ahead with Gamechanging Li-Ion Batteries



## Battery Manufacturing Process Application Guide

	1	2	3	4	5	6	7	8	9
	Mixing	Coating	Slitting / Notching	Tab Welding	Stacking	Electrolyte Injection	Degassing	Formation	Testing
<b>ÖLFLEX®</b> Power and control cables									
ÖLFLEX® CLASSIC 100 CY			●		●				
ÖLFLEX® CLASSIC 110 / 110 CY	●	●	●	●	●	●	●	●	
ÖLFLEX® CLASSIC 110 BK 0.6/1KV	●								
ÖLFLEX® CLASSIC 110H / 110CH	●	●					●		
ÖLFLEX® CLASSIC 115 CY		●				●	●	●	
ÖLFLEX® CLASSIC 130H	●	●	●		●		●	●	●
ÖLFLEX® CLASSIC 135CH	●	●					●	●	●
ÖLFLEX® CLASSIC 6130H / 6130CH	●							●	
ÖLFLEX® CLASSIC 6135CH	●							●	
ÖLFLEX® CLASSIC 400 P								●	
ÖLFLEX® 150 QUATTRO		●				●	●		
ÖLFLEX® 191 / 191 CY	●	●	●		●	●	●	●	
ÖLFLEX® 191K / 191K CY	●	●	●		●	●	●	●	
ÖLFLEX® FD 810		●				●	●	●	
ÖLFLEX® FD 855 P / 855 CP		●					●	●	●
ÖLFLEX® FD 891 / 891 CY		●				●	●		
ÖLFLEX® FD 90 / 90 CY	●					●		●	
ÖLFLEX® CHAIN 809 SC	●	●					●		
ÖLFLEX® CHAIN 819 P / 819 CP				●		●			
ÖLFLEX® ROBOT 900 P / 900 DP		●		●		●	●	●	
ÖLFLEX® ROBOT F1		●					●		●
ROBOCABLE F1						●			
ÖLFLEX® SERVO FD 796 CP			●	●	●				
ÖLFLEX® SERVO FD 798 CP			●	●	●				
ÖLFLEX® SERVO 2XSLCH-JB	●								
ÖLFLEX® SERVO 2YSLCYK-JB		●					●		
H05V-K	●	●				●	●	●	
H05Z-K 90°C						●			
H07V-K	●	●				●	●	●	
H07Z-K 90°C	●	●	●		●		●	●	●
Multi-Standard SC 2.1	●	●				●	●	●	
NSGAFOU 1,8/3kV				●				●	
ÖLFLEX® WIRE 1063 SC	●							●	
ÖLFLEX® HEAT 125 SC	●	●					●	●	●
ÖLFLEX® HEAT 180 SIF / SIF A		●					●		
ÖLFLEX® HEAT 180 SIHF		●				●			
ÖLFLEX® HEAT 180 EWKF		●					●		
ÖLFLEX® HEAT 205 SC		●					●		
ÖLFLEX® HEAT 260 C								●	
ÖLFLEX® HEAT 350 SC		●	●		●		●		
ÖLFLEX® TRAIN 3GKW SC								●	
ÖLFLEX® DC ESS SC	●							●	
ÖLFLEX® DC ESS SC U		●					●	●	
ÖLFLEX® CONTROL TM		●				●	●		
ÖLFLEX® TRAY II						●			
<b>ETHERLINE®</b> Data communication systems for ETHERNET technology									
ETHERLINE® FD P CAT.5	●	●		●			●		
ETHERLINE® FD P CAT.6	●								
ETHERLINE® FD P FC UL/CSA CAT.5						●		●	●
ETHERLINE® H CAT.5e		●	●		●		●	●	●
ETHERLINE® PN CAT.5e Y	●			●					
ETHERLINE® PN CAT.5e FRNC FLEX FC						●		●	●
ETHERLINE® Y FC UL/CSA CAT.5	●		●		●				
ETHERLINE® LAN CAT.6A S/FTP						●		●	
ETHERLINE® LAN 1000 S/FTP CAT.7A LSZH									●
TOSIBOX®	●	●	●	●	●	●	●	●	●
<b>UNITRONIC®</b> Data communication systems									
UNITRONIC® LiYY / LiYY A		●		●			●		
UNITRONIC® LiYCY / LiYCY A		●		●		●	●	●	
UNITRONIC® Li2YCY PiMF								●	●
UNITRONIC® LiHCH / LiHCH TP	●	●				●	●	●	●
UNITRONIC® LiHH	●	●					●	●	●
UNITRONIC® BUS CAN	●	●					●	●	
UNITRONIC® BUS CC		●	●		●		●		
UNITRONIC® BUS CC FD P FRNC			●		●				
UNITRONIC® FD		●		●			●	●	
UNITRONIC® FD P Plus								●	●
UNITRONIC® FD CP (TP) Plus A						●		●	
UNITRONIC® LAN 600 S						●			
<b>ÖLFLEX® CONNECT</b>									
ÖLFLEX® CONNECT CABLE SOLUTION	●	●	●	●	●	●	●	●	●
<b>EPIC®</b> Industrial connectors									
EPIC® POWER LS1	●	●	●	●	●	●	●	●	●
EPIC® SIGNAL M23	●	●	●	●	●	●	●	●	●
EPIC® DATA RJ45	●	●	●	●	●	●	●	●	●
EPIC® DATA M12D	●	●	●	●	●	●	●	●	●
<b>SKINTOP®</b> Cable glands									
SKINTOP® metallic glands	●	●	●	●	●	●	●	●	●
SKINTOP® non-metallic glands	●	●	●	●	●	●	●	●	●
SKINTOP® CUBE	●	●	●	●	●	●	●	●	●
SKINTOP® MULTI	●	●	●	●	●	●	●	●	●
SKINTOP® CLICK	●	●	●	●	●	●	●	●	●
<b>SILVYN®</b> Protective cable conduit systems and cable carrier systems									
SILVYN® conduit	●	●	●	●	●	●	●	●	●
<b>FLEXIMARK®</b> Marking systems									
FLEXIMARK® Cable Markers	●	●	●	●	●	●	●	●	●